

HID-HeavyDuty BHL for HPL/HPI

BHL 400 L40-A2 230V 50Hz HD2-151

Encapsulated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps


Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BHL 400 L40-A2 230V 50Hz HD2-151

Full product name	BHL 400 L40-A2 230V 50Hz HD2-151
Full product code	871150091953330
Order code	913604920426
Material Nr. (12NC)	913604920426
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500919533
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500934703

HID-HeavyDuty BHL for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 400 L40-A2 230V 50Hz HD2-151	6.2 mm	66.0 mm	151.0 mm	132.5 mm	81.0 mm

