



Image
not
available

Pole gear trays EGS350

EGS350 2xHPI-T400W LV

EGS350, 2, HPI-T High Wattage, 400 W

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

Product data

General Information	
Lamp family code	HPI-T [HPI-T High Wattage]
Product family code	EGS350 [EGS350]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	230 V
Power Consumption	400 W
Approval and Application	
Ingress protection code	IP21 [Finger-protected, drip-proof]

Protection class IEC	Safety class I
Product Data	
Order product name	EGS350 2xHPI-T400W LV
Full product name	EGS350 2xHPI-T400W LV
Full product code	871155984883900
Order code	913616010418
Material Nr. (12NC)	913616010418
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559848839
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559848839

Pole gear trays EGS350

Dimensional drawing

