

Gear for SDW-T lamps

CSLS 100 SDW-T 220-240V 50/60Hz

CSLS electronic control unit with impregnated (HID 'BASIC') or encapsulated (HID 'Heavy Duty') electromagnetic ballasts

Warnings and Safety

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)


Product data

| Operating and Electrical | |
|----------------------------------|---|
| Input Voltage | 220 to 240 V |
| Input Frequency | 50 to 60 Hz |
| Wiring | |
| Cable Length From Device to Lamp | 0.50 m |
| Connector Type | Screw |
| Temperature | |
| T-Case Lifetime (Nom) | 90 °C |
| T-Case Maximum (Max) | 90 °C |
| Approval and Application | |
| Approval Marks | CE marking VDE-EMV certificate CB Certificate |

| Product Data | |
|---------------------------------|---------------------------------|
| Order product name | CSLS 100 SDW-T 220-240V 50/60Hz |
| Full product name | CSLS 100 SDW-T 220-240V 50/60Hz |
| Full product code | 871150090870430 |
| Order code | 913619189966 |
| Material Nr. (12NC) | 913619189966 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500908704 |
| Numerator - Packs per outer box | 18 |
| EAN/UPC - Case | 8711500908711 |

Gear for SDW-T lamps

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 | B2 |
|------------------------------------|--------|---------|---------|---------|---------|---------|
| CSLS 100 SDW-T 220-240V 50/60Hz | 4.5 mm | 39.5 mm | 98.0 mm | 70.0 mm | 58.5 mm | 46.0 mm |

