



# HID-Constant wattage BSX for SOX

## BSX 180 H96 220-240V 50Hz CW-178/78


Constant-wattage (potted) electromagnetic copper/iron ballasts for use with an external ignitor for SOX and SOX-E lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSX 180 H96 220-240V 50Hz CW-178/78	
Input Voltage	220 to 240 V	Full EOC		871150093900599	
Line Frequency	50 Hz	Order code		93900599	
Input frequency	50 Hz	Material no. (12 NC)		913626027226	
		SAP numerator – quantity per pack		1	
		EAN/UPC — Product/Case		8711500939005	
		Numerator – packs per outer box		4	
		EAN/UPC – Case		8711500932167	
<b>Wiring</b>					
Connector type	Screw				
<b>Approval and Application</b>					
Approval marks	CE marking ENEC certificate				
<b>Product Data</b>					
Order product name	BSX 180 H96 220-240V 50Hz CW-178/78				

# HID-Constant wattage BSX for SOX

## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
BSX 180 H96 220-240V	4.2 mm	78.0 mm	178.0 mm	162.0 mm	100.0 mm	42.0 mm
50Hz CW-178/78						

