

LuxSense


LRL1220 TL-D

LuxSense is a DayLight Regulation option (DLR) for luminaires equipped with a Philips HFR ballast. The sensor measures the reflected light coming from the surface below. It dims down the lamp output when the light level exceeds the required light level defined by the light sensor set point. LuxSense can be installed in the luminaire by attaching it to the lamp with a lamp clip. LuxSense is available as a complete set with a sensor and a lamp clip: LRL1220 TL-D for TLD lamps and LRL1220 TL5 for T5 lamps.

Product data

Product Data		Local order code	
Order product name	LRL1220 TL-D	Numerator - Quantity Per Pack	1
Full product name	LRL1220 TL-D	EAN/UPC - Product/Case	8711559670126
Full product code	871155967012630	Numerator - Packs per outer box	100
Local code description	LRL1220TLD	EAN/UPC - Case	8711559670133
Order code	913700182282		
Material Nr. (12NC)	913700182282		

Dimensional drawing



Product
LRL1220 TL-D

