



HID-HighPower for SON/MH/HPL/HPI

BSN 1000 L78 230/240V 50HZ HP-257


Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

Product data

Operating and Electrical		Full product name	BSN 1000 L78 230/240V 50HZ HP-257
Input Voltage	230 V (default) or 240 V	Full EOC	871150006236900
Line Frequency	50 Hz	Local code description	BSN1000L78
Input frequency	50 Hz	Order code	06236900
Wiring		Material no. (12 NC)	913700217503
Connector type	Screw	Local order code	BSN1000L78
Approval and Application		SAP numerator – quantity per pack	1
Approval marks	CE marking ENEC certificate	EAN/UPC – Product/Case	8711500996640
Product Data		Numerator – packs per outer box	1
Order product name	BSN 1000 L78-A2 230/240V 50Hz HP-257	EAN/UPC - Case	8711500062369

HID-HighPower for SON/MH/HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BSN 1000 L78-A2	6.5	102.0	257.0	222.0	246.0	117.0	88.0
230/240V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-257							

