



# HID-HighPower for SON/MH/HPL/HPI

## BMH 1800 L78 230/240V 50Hz HP-317

Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

### Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BMH 1800 L78 230/240V 50Hz HP-317

Full product name	BMH 1800 L78 230/240V 50Hz HP-317
Full product code	871150005990100
Order code	913700217703
Material Nr. (12NC)	913700217703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500996572
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500059901

HID-HighPower for SON/MH/HPL/HPI

Dimensional drawing

Product	D1	C1	A1	A2	A3	B1	B2
BMH 1800 L78	6.5	102.0	317.0	282.0	306.0	117.0	88.0
230/240V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-317							

