



HID-HighPower for SON/MH/HPL/HPI

BHL 2000 L76 380/400/415V 50HZ HP-317


Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000W and above

Product data

Operating and Electrical		Full product name		BHL 2000 L76 380/400/415V 50HZ HP-317
Input Voltage	380 to 415 V	Full product code		871150006384700
Line Frequency	50 Hz	Order code		06384700
Input Frequency	50 Hz	Material Nr. (12NC)		913700217903
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8711500996664
		Numerator - Packs per outer box		1
		EAN/UPC - Case		8711500063847
Approval and Application				
Approval Marks	CE marking ENEC certificate			
Product Data				
Order product name	BHL 2000 L76-A2 380/400/415V 50Hz HP-317			

HID-HighPower for SON/MH/HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BHL 2000 L76-A2	6.5	102.0	317.0	282.0	306.0	117.0	88.0
380/400/415V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-317							

