



HID-HighPower for SON/MH/HPL/HPI

BSN 1000 L02 220V 50Hz HP-257

Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

Product data

Operating and Electrical		Full product name		BSN 1000 L02 220V 50Hz HP-257	
Input Voltage	220 V	Full product code		871150006228400	
Line Frequency	50 Hz	Order code		913700218103	
Input Frequency	50 Hz	Material Nr. (12NC)		913700218103	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8711500996602	
		Numerator - Packs per outer box		1	
		EAN/UPC - Case		8711500062284	
Wiring					
Connector Type	Screw				
Approval and Application					
Approval Marks	CE marking ENEC certificate				
Product Data					
Order product name	BSN 1000 L02 220V 50Hz HP-257				

HID-HighPower for SON/MH/HPL/HPI

Dimensional drawing

Product	D1	C1	A1	A2	A3	B1	B2
BSN 1000 L02	6.5 mm	102.0	257.0	222.0	246.0	117.0	88.0
220V 50Hz		mm	mm	mm	mm	mm	mm
HP-257							

