

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 70 L34-TS 240V 50Hz HD1-118


Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 70 L34-TS 240V 50Hz HD1-118	
Input Voltage	240 V	Full EOC		871150005970331	
Line Frequency	50 Hz	Order code		05970331	
Input frequency	50 Hz	Material no. (12 NC)		913700226626	
Wiring		SAP numerator – quantity per pack		1	
Connector type	Screw	EAN/UPC — Product/Case		8711500059703	
		Numerator – packs per outer box		6	
		EAN/UPC - Case		8711500062161	
Approval and Application					
Approval marks	CE marking ENEC certificate				
Product Data					
Order product name	BSN 70 L34-A2-TS 240V 50Hz HD1-118				

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 70 L34-A2-TS 240V 50Hz	6.2 mm	53.0 mm	118.0 mm	103.0 mm	65.0 mm
HD1-118					

