



HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 100 L33-TS 230V 50Hz HD1-123

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 100 L33-TS 230V 50Hz HD1-123	
Input Voltage	230 V	Full product code		871150005972731	
Line Frequency	50 Hz	Order code		913700226726	
Input Frequency	50 Hz	Material Nr. (12NC)		913700226726	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8711500059727	
		Numerator - Packs per outer box		6	
		EAN/UPC - Case		8711500061614	
Approval and Application					
Approval Marks		CE marking ENEC certificate			
Product Data					
Order product name		BSN 100 L33-TS 230V 50Hz HD1-123			

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing

Product	D1	C1	A1	A2	B1
BSN 100 L33-TS 230V 50Hz HD1-123	6.2 mm	53.0 mm	123.0 mm	108.0 mm	65.0 mm

