

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 400 L33-TS 230V 50Hz HD3-166


Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 400 L33-TS 230V 50Hz HD3-166	
Input Voltage	230 V	Full product code		871150005976530	
Line Frequency	50 Hz	Order code		05976530	
Input Frequency	50 Hz	Material Nr. (12NC)		913700226926	
Wiring		Numerator - Quantity Per Pack		1	
Connector Type	Screw	EAN/UPC - Product/Case		8711500059765	
Approval and Application		Numerator - Packs per outer box		4	
Approval Marks	CE marking ENEC certificate	EAN/UPC - Case		8711500059772	
Product Data					
Order product name	BSN 400 L33-A2-TS 230V 50Hz HD3-166				

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400 L33-A2-TS 230V 50Hz	6.2 mm	84.0 mm	166.0 mm	147.5 mm	102.0 mm
HD3-166					

