



# HID-HighPower for SON/MH/HPL/HPI

## BHD 2000 L76 380/400/415V 50Hz HP-317


Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BHD 2000 L76 380/400/415V 50Hz HP-317
<b>Input Voltage</b>	380 to 415 V	<b>Full product code</b>		871150074276600
<b>Line Frequency</b>	50 Hz	<b>Order code</b>		74276600
<b>Input Frequency</b>	50 Hz	<b>Material Nr. (12NC)</b>		913700232103
		<b>Numerator - Quantity Per Pack</b>		1
		<b>EAN/UPC - Product/Case</b>		8711500996695
		<b>Numerator - Packs per outer box</b>		1
		<b>EAN/UPC - Case</b>		8711500742766
<b>Approval and Application</b>				
<b>Approval Marks</b>	CE marking ENEC certificate			
<b>Product Data</b>				
<b>Order product name</b>	BHD 2000 L76-A2 380/400/415V 50Hz HP-317			

# HID-HighPower for SON/MH/HPL/HPI

## Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BHD 2000 L76-A2	6.5	102.0	317.0	282.0	306.0	117.0	88.0
380/400/415V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-317							

