



HID-HighPower for SON/MH/HPL/HPI

BHD 2000 L76-A2 380/400/415V 50Hz HP-317


Encapsulated ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

Product data

Operating and Electrical		Full product name		BHD 2000 L76-A2 380/400/415V 50Hz HP-317
Input Voltage	380 to 415 V	Full product code		871150074276600
Line Frequency	50 Hz	Order code		913700232103
Input Frequency	50 Hz	Material Nr. (12NC)		913700232103
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8711500996695
		Numerator - Packs per outer box		1
		EAN/UPC - Case		8711500742766
Approval and Application				
Approval Marks	CE marking ENEC certificate			
Product Data				
Order product name	BHD 2000 L76-A2 380/400/415V 50Hz HP-317			

HID-HighPower for SON/MH/HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BHD 2000 L76-A2	6.5	102.0	317.0	282.0	306.0	117.0	88.0
380/400/415V 50Hz	mm	mm	mm	mm	mm	mm	mm
HP-317							

