



# HID-Basic BHL MK4 for HPL/HPI

## BHL 250 K307 230/240V 50Hz BC2-134

Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps


### Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BHL 250 K307-A2 230/240V 50Hz BC2-134

Full product name	BHL 250 K307 230/240V 50Hz BC2-134
Full product code	872790088701300
Order code	88701300
Material Nr. (12NC)	913700278026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881588
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900887013

# HID-Basic BHL MK4 for HPL/HPI

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250 K307-A2 230/240V 50Hz	6.2 mm	65.0 mm	134.0 mm	113.0 mm	76.0 mm
BC2-134					

