

HID-Basic BHL MK4 for HPL/HPI

BHL 400 K327-A2 230/240V 50Hz BC2-160


Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

Product data

Operating and Electrical		Full product name		BHL 400 K327-A2 230/240V 50Hz BC2-160
Input Voltage	230 V (default) or 240 V	Full product code		872790088919200
Line Frequency	50 Hz	Order code		913700278327
Input Frequency	50 Hz	Material Nr. (12NC)		913700278327
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8711500999016
		Numerator - Packs per outer box		268
		EAN/UPC - Case		8727900889192
Approval and Application				
Approval Marks	CE marking ENEC certificate			
Product Data				
Order product name	BHL 400 K327-A2 230/240V 50Hz BC2-160			

HID-Basic BHL MK4 for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 400 K327-A2 230/240V 50Hz	6.2 mm	65.0 mm	160.0 mm	139.0 mm	76.0 mm
BC2-160					

