

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 400 K302-I 230V 50Hz BC3-166


Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 400 K302-I 230V 50Hz BC3-166	
Input Voltage	230 V	Full product code		872790094088600	
Line Frequency	50 Hz	Order code		913700281926	
Input Frequency	50 Hz	Material Nr. (12NC)		913700281926	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8727900940886	
		Numerator - Packs per outer box		2	
		EAN/UPC - Case		8727900940893	
Approval and Application					
Approval Marks		CE marking ENEC certificate			
Product Data					
Order product name		BSN 400 K302-I 230V 50Hz BC3-166			

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400 K302-I 230V 50Hz	6.3 mm	83.0 mm	166.0 mm	144.0 mm	97.0 mm
BC3-166					

