

# HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

## BSN 50/70 K322-TS-R


Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

### Product data

<b>Wiring</b>		<b>Full product code</b>		872790094045900
Connector Type	Screw	Order code	913700282226	
<b>Approval and Application</b>		Material Nr. (12NC)	913700282226	
<b>Approval Marks</b>		Numerator - Quantity Per Pack	1	
<b>Product Data</b>		EAN/UPC - Product/Case	8727900940459	
Order product name	BSN 50/70 K322-TS-R	Numerator - Packs per outer box	6	
Full product name	BSN 50/70 K322-TS-R	EAN/UPC - Case	8727900940466	

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	C1	A1	B1
BSN 50/70 K322-TS-R	52.0 mm	118.0 mm	61.0 mm

