

HID-Basic BHL for HPL/HPI

BHL 250 K202 230V 50Hz BC2-126


Impregnated electromagnetic copper/iron ballasts for HPL and HPI (Plus) lamps

Product data

Operating and Electrical		Full product name		BHL 250 K202 230V 50Hz BC2-126
Input Voltage	230 V	Full product code		872790094064000
Line Frequency	50 Hz	Order code		94064000
Input Frequency	50 Hz	Material Nr. (12NC)		913700283226
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8727900940640
		Numerator - Packs per outer box		6
		EAN/UPC - Case		8727900940657
Approval and Application				
Approval Marks	CE marking ENEC certificate			
Product Data				
Order product name	BHL 250 K202-A2 230V 50Hz BC2-126			

HID-Basic BHL for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250 K202-A2 230V 50Hz	6.2 mm	65.0 mm	126.0 mm	104.0 mm	76.0 mm
BC2-126					

