



HID-Basic BHL for HPL/HPI

BHL 250 K202-A2 230V 50Hz BC2-126


Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps

Product data

Operating and Electrical		Full product name	
Input Voltage	230 V		BHL 250 K202-A2 230V 50Hz BC2-126
Line Frequency	50 Hz	Full product code	872790094064000
Input Frequency	50 Hz	Order code	913700283226
Wiring		Material Nr. (12NC)	913700283226
Connector Type	Screw	Numerator - Quantity Per Pack	1
Approval and Application		EAN/UPC - Product/Case	8727900940640
Approval Marks	CE marking ENEC certificate	Numerator - Packs per outer box	6
Product Data		EAN/UPC - Case	8727900940657
Order product name	BHL 250 K202-A2 230V 50Hz BC2-126		

HID-Basic BHL for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250 K202-A2 230V 50Hz	6.2 mm	65.0 mm	126.0 mm	104.0 mm	76.0 mm
BC2-126					

