

HID-Basic BHL for HPL/HPI

BHL 125 K307 230/240V 50Hz BC1-118

Impregnated electromagnetic copper/iron ballasts for HPL, HPI (Plus) and SON-H lamps


Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BHL 125 K307 230/240V 50Hz BC1-118

Full product name	BHL 125 K307 230/240V 50Hz BC1-118
Full product code	872790094005300
Order code	913700286026
Material Nr. (12NC)	913700286026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900940053
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900940060

HID-Basic BHL for HPL/HPI

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 125 K307 230/240V 50Hz BC1-118	6.2 mm	52.0 mm	118.0 mm	94.0 mm	61.0 mm

