



# HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

## BSN 400/250 K407-TS 230/240V 50Hz

Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

### Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSN 400/250 K407-TS 230/240V 50Hz

Full product name	BSN 400/250 K407-TS 230/240V 50Hz
Full product code	872790094086200
Order code	913700286426
Material Nr. (12NC)	913700286426
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900940862
Numerator - Packs per outer box	2
EAN/UPC - Case	8727900940879

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Dimensional drawing

Product	C1	A1	B1
BSN 400/250 K407-TS 230/240V 50Hz	83.0 mm	166.0 mm	97.0 mm

