



# HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

## BSN 150/100 K427-TS 230/240V 50Hz

Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 150/100 K427-TS 230/240V 50Hz	
<b>Input Voltage</b>	230 V (default) or 240 V	<b>Full product code</b>		872790095370100	
<b>Line Frequency</b>	50 Hz	<b>Order code</b>		913700286827	
<b>Input Frequency</b>	50 Hz	<b>Material Nr. (12NC)</b>		913700286827	
		<b>Numerator - Quantity Per Pack</b>		1	
		<b>EAN/UPC - Product/Case</b>		8727900953701	
		<b>Numerator - Packs per outer box</b>		415	
		<b>EAN/UPC - Case</b>		8727900953718	
<b>Wiring</b>					
<b>Connector Type</b>	Screw				
<b>Approval and Application</b>					
<b>Approval Marks</b>	CE marking ENEC certificate				
<b>Product Data</b>					
<b>Order product name</b>	BSN 150/100 K427-TS 230/240V 50Hz				

HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Dimensional drawing

Product	C1	A1	B1
BSN 150/100 K427-TS 230/240V 50Hz	65.0 mm	134.0 mm	76.0 mm

