

HID-Basic BSN/BMH series for SON/CDO/MH/HPI

BSN 150 K307-TS-R 230/240V 50Hz BC2-134

Impregnated electromagnetic copper/iron ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps (no ignitor needed for SON-I lamps)

Warnings and Safety


- Climatic suitability: restricted to built-in situations where relative humidity is limited

Product data

Operating and Electrical		Full product name	
Input Voltage	230 V (default) or 240 V	Full product code	871829120611800
Line Frequency	50 Hz	Order code	913700292126
Input Frequency	50 Hz	Material Nr. (12NC)	913700292126
Wiring		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	8718291206118
Approval and Application		Numerator - Packs per outer box	6
Approval Marks	CE marking ENEC certificate	EAN/UPC - Case	8718291206125
Product Data			
Order product name	BSN 150 K307-TS-R 230/240V 50Hz BC2-134		

HID-Basic BSN/BMH series for SON/CDO/MH/HPI

Dimensional drawing



Product	C1	A1	A2	B1
BSN 150 K307-TS-R 230/240V 50Hz BC2-134	65.0 mm	134.0 mm	113.0 mm	76.0 mm

