



HID-Basic BSN/BMH series for SON/CDO/MH/HPI

BSN 70 K307-TS-R 230/240V 50Hz BC1-118

Impregnated electromagnetic copper/iron ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps (no ignitor needed for SON-I lamps)

Warnings and Safety


- Climatic suitability: restricted to built-in situations where relative humidity is limited

Product data

Operating and Electrical		Full product name		BSN 70 K307-TS-R 230/240V 50Hz BC1-118
Input Voltage	230 V (default) or 240 V	Full product code		871829120605700
Line Frequency	50 Hz	Order code		913700293126
Input Frequency	50 Hz	Material Nr. (12NC)		913700293126
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8718291206057
		Numerator - Packs per outer box		6
		EAN/UPC - Case		8718291206064
Approval and Application				
Approval Marks	CE marking ENEC certificate			
Product Data				
Order product name	BSN 70 K307-TS-R 230/240V 50Hz BC1-118			

HID-Basic BSN/BMH series for SON/CDO/MH/HPI

Dimensional drawing



Product	C1	A1	B1
BSN 70 K307-TS-R 230/240V 50Hz BC1-118	52.0 mm	118.0 mm	61.0 mm

