



ActiLume 1-10V

LRI1655/00 ActiLume 1-10V Sensor 100 Cm


ActiLume 1-10 V can be connected to the 1-10 V DC control input of an HF-R ballast.
ActiLume 1-10 V is calibrated for use in a standard office situation.

产品数据

产品数据	
订单产品名称	LRI1655/00 ActiLume 1-10V Sensor 100 Cm
完整的产品名称	LRI1655/00 ActiLume 1-10V Sensor 100 Cm
完整产品代码	872790094298900
订购代码	913700339503
材料编号 (12NC)	913700339503

计算器 - 每包数量	1
EAN/UPC - 产品/箱	8727900942989
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8727900942996

二维绘图



Product
LRI1655/00 ActiLume 1-10V Sensor 100 Cm