



OccuSwitch

LRM1075/00 SENSOR MOV DET ST CH

The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m². A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling

Product data

| Product Data | |
|---------------------|---------------------------------|
| Order product name | LRM1075/00 SENSOR MOV DET ST CH |
| Full product name | LRM1075/00 SENSOR MOV DET ST CH |
| Full product code | 871829113733700 |
| Order code | 913700344670 |
| Material Nr. (12NC) | 913700344670 |

| | |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291137337 |
| Numerator - Packs per outer box | 42 |
| EAN/UPC - Case | 8718291137344 |

Dimensional drawing

