



OccuSwitch

LRM1040/00 OS Mov Det Ip44 180Dgr


The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m². A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling, a separate Wieland cable is available for easy, fast and trouble-free installation.

Product data

Product Data	
Order product name	LRM1040/00 OS Mov Det IP54 240 dgr
Full product name	LRM1040/00 OS Mov Det Ip44 180Dgr
Full product code	871829122573700
Order code	22573700
Material Nr. (12NC)	913700350903

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291225737
Numerator - Packs per outer box	36
EAN/UPC - Case	8718291225744

Dimensional drawing



Product

LRM1040/00 OS Mov Det IP54 240 dgr