



# OccuSwitch

## LRM1032/00 OS Mov Det Switch 3w WR DIN


The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m<sup>2</sup>. A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling, a separate Wieland cable is available for easy, fast and trouble-free installation.

### Product data

Product Data	
Order product name	LRM1032/00 OS Mov Det Switch 3w WR DIN
Full product name	LRM1032/00 OS Mov Det Switch 3w WR DIN
Full EOC	871869644225800
Order code	44225800
Material no. (12 NC)	913700359603

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696442258
Numerator – packs per outer box	1
EAN/UPC - Case	8718696442265

### Dimensional drawing



Product
LRM1032/00 OS Mov Det Switch 3w WR DIN