



# OccuSwitch

## LRM1032/00 OS Mov Det Switch 3w WR DIN


The OccuSwitch is a movement detector with a built-in switch. It will switch the lights off in a room or area when it is vacated and thus save up to 30% on electricity. The OccuSwitch can switch any load of up to 6 A and control an area of between 20 and 25 m². A detachable mains connector enables easy installation and mounting of the OccuSwitch in the ceiling

### Product data

Product Data	
Order product name	LRM1032/00 OS Mov Det Switch 3w WR DIN
Full product name	LRM1032/00 OS Mov Det Switch 3w WR DIN
Full product code	871869644225800
Order code	913700359603
Material Nr. (12NC)	913700359603

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696442258
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696442265

### Dimensional drawing



#### Product

LRM1032/00 OS Mov Det Switch 3w WR DIN