



# ActiLume 1-10V

## LRM1657/05 ActiLume 1-10V Ind Mov Sensor

The ActiLume 1-10 V system consists of a sensor and a SwitchBox (controller) designed for easy integration into luminaires. The sensor can work independently of the SwitchBox. In combination with the SwitchBox, the luminaire will be switched off when enough daylight is present and/or when no presence is detected. The ActiLume 1-10 V luminaire-based sensor enables daylight regulation and dimming when no presence is detected. The delay time can be customized between 1 and 30 minutes.

### Product data

Product Data		Numerator - Quantity Per Pack	
Order product name	LRM1657/05 ActiLume 1-10V Ind Mov Sensor		1
Full product name	LRM1657/05 ActiLume 1-10V Ind Mov Sensor	EAN/UPC - Product/Case	8718696524947
Full product code	871869652494700	Numerator - Packs per outer box	192
Order code	913700369103	EAN/UPC - Case	8718696524961
Material Nr. (12NC)	913700369103		

### Dimensional drawing

