



Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID HPS BAL 50W S68 120V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information			
ANSI Code	S68	Input Frequency	60 Hz
Lamp Type	50W HPS	Input Current (Open Circuit)	0.9 A
Number of Lamps	1 piece/unit	Input Current (Starting)	0.95 A
Circuit Type	R-HPF	Input Current (Short Circuit)	1.45–2.2 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	1.45–2.2 A
Base Model	71A7807B	Constant Wattage Deviation	Within Trapezoid
Core Size	2 5/8 x 2 3/16	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	INTEGRAL	Open Circuit Voltage	120 V
Ignitor Temperature Rating	125°C	Input Current (Nom)	0.55 A A
Capacitor Value	20 MFD	Input Power (Nom)	62 W
Capacitor Catalog Number	7C200M12RA	Rated Lamp Power	50 W
Capacitor Requirements	120V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.25 in	Wire Length by Color	12"
Capacitor Height	2.75 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote Wiring	2'
Input Voltage	120 V	Recommended Fuse Value	3 A

Core & Coil (71A) HPS ~LT~ 200W

Approval and Application


Open Circuit Voltage Test (Volts)	114-126 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

Product Data

Order product name	CORE & COIL HID HPS BAL 50W S68 120V KIT
--------------------	---

EAN/UPC - Product	781087026274
Order code	132092
Local order code	132092
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700500881
Net Weight (Piece)	0.894 kg

Dimensional drawing



HPS BAL 50W S68 120V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 50W S68 120V KIT	2.7 in	0.95 in	2.6 in	2.2 in	2.2 in	1.8 in

