



Standard

STANDARD MAG BALLAST (1) FC8T9 CIRCLINE 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

Product data

General Information	
Lamp Type	FC8T9
Number of Lamps	1 piece/unit
Lamp Footage	-
Ballast Type	Magnetic Fluorescent
Base Model	RLQS122TPW
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	120 V
Input Frequency	60 Hz
Max THD	10 %
Starting Method	Rapid Start
Lamp Current Crest Factor (Nom)	1.5
Ignition Time (Nom)	1 s
Ballast Factor (Nom)	0.75
Power Factor (Nom)	0.39
Input Current (Operating) (Nom)	0.53 A
Input Power (Nom)	25 W
Rated Lamp Watts	22 W

Wiring	
Wire Striplength	0.50/0.375 mm
Lamp Connection	Series
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Max Ballast-Lamp Distance Remote Wiring	30'
Max Ballast-Lamp Distance Tandem Wiring	-
Max Ballast-Lamp Distance Through Wiring	-

Mechanical and Housing	
Housing Material	Metal
Housing	R4
Housing Dimensions	6.5" x 1.94" x 1.38"


Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate RoHS Compliant
Sound Rating	A

Standard

UL Recognized	No
Product Data	
Order product name	STANDARD MAG BALLAST (1) FC8T9 CIRCLINE 120V
EAN/UPC - Product	781087053546
Order code	RLQS122TPWI

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913700501111
Net Weight (Piece)	0.940 kg

Dimensional drawing



Product	A1	A2	B1	C1
STANDARD MAG BALLAST (1) FC8T9 CIRCLINE 120V	6.5 in	6 in	1.94 in	1.38 in

MAG BALLAST (1) FC8T9 CIRCLINE 120V

