



Core & Coil (71A) HPS ~GT~ 400W

CORE & COIL HID HPS BAL 1000W S52 QUAD C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data


General Information			
ANSI Code	S52	Input Frequency	60 Hz
Lamp Type	1000W HPS	Inp. Current (Open Circuit)	4.8/2.7/2.4/2.2 A
Number of Lamps	1 piece/unit	Input Current (Starting)	6.4/3.8/3.2/2.8 A
Circuit Type	CWA	Input Current (Short Circuit)	5.2-7.8/3-4.5/2.6-3.8/2.25-3.4 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	6.4-7.8 A
Base Model	71A8793	Constant Wattage Deviation	Within Trapezoid
Core Size	4 1/4 x 6	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI571-H5	Nominal Open Circuit Voltage	441 V
Ignitor Temperature Rating	105°C	Input Current (Operating) (Nom)	9.5/5.5/4.75/4.15 A A
Capacitor Value	26 MFD	Input Power (Nom)	1100 W
Capacitor Catalog Number	RW1626020	Rated Lamp Watts	1000 W
Capacitor Requirements	525V	Wiring	
Capacitor Temperature Rating	90°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.75 in	Wire Length by Color	12"
Capacitor Height	4.25 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote	15'
Input Voltage	120/208/240/277 V	Wiring	

Core & Coil (71A) HPS ~GT~ 400W

Recommended Fuse Value	25/15/10/10 A
Approval and Application	
Open Circuit Voltage Test (Volts)	395-485 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/B/C/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

Product Data	
Order product name	CORE & COIL HID HPS BAL 1000W S52 QUAD C&C
EAN/UPC - Product	781087038062
Order code	71A8793600
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	913700506131
Net Weight (Piece)	12.774 kg

Dimensional drawing



HPS BAL 1000W S52 QUAD C&C

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID HPS BAL 1000W S52 QUAD C&C	5.75 in	3.75 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

