



Standard

STANDARD MAG BALLAST (1) 9W COMPACT(2-PIN) 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

Product data


General Information		Rated Lamp Power	9 W
Lamp Type	CFQ9W/G23	Wiring	
Number of Lamps	1 piece/unit	Wire Striplength	0.50/0.375 mm
Lamp Footage	-	Lamp Connection	Series
Ballast Type	Magnetic Fluorescent	Wire Length by Color	See data sheet
Base Model	H1B9TPW	Wire Gauge (Nom)	18AWG mm
Suitable For Outdoor Use	Yes	Wire Type	Solid
Automatic Restart	Yes	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Tandem Wiring Configuration Allowed	No
Input Voltage	120 V	Through Wiring Configuration Allowed	No
Input Frequency	60 Hz	Max Ballast-Lamp Distance Remote Wiring	30'
Total Harmonic Distortion USA	20 %	Max Ballast-Lamp Distance Tandem Wiring	-
Ignition Method	Preheat	Max Ballast-Lamp Distance Through Wiring	-
Crestfactor (Nom)	1.5	Mechanical and Housing	
Ignition Time (Nom)	1 s	Housing Material	Metal
Input Current (Open Circuit)	0.13	Housing	R1
Input Current (Starting)	0.2	Housing Dimensions	4.25" x 2.0" x 1.44"
Ballast Factor (Nom)	0.92	Approval and Application	
Power Factor (Nom)	0.91	EMC Immunity Standard	FCC Non-Consumer
Input Current (Nom)	0.1 A		
Input Power (Nom)	11 W		

Standard

Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No
Product Data	
Order product name	STANDARD MAG BALLAST (1) 9W COMPACT(2-PIN) 120V
EAN/UPC - Product	781087068281

Order code	173930
Local order code	173930
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36
Material Nr. (12NC)	913700506409
Net Weight (Piece)	314.000 g

Dimensional drawing



MAG BALLAST (1) 9W COMPACT(2-PIN) 120V

Product	A1	A2	B1	C1
STANDARD MAG BALLAST (1) 9W COMPACT(2-PIN) 120V	4.25 in	3.56 in	2 in	1.44 in

