



Standard

STANDARD MAG BALLAST (1) 26W COMPACT(2-PIN) 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

Product data


General Information		Rated Lamp Watts	
Lamp Type	CFQ26W/G24D	26 W	
Number of Lamps	1 piece/unit		
Lamp Footage	-		
Ballast Type	Magnetic Fluorescent		
Base Model	HIQ26TPW		
Suitable For Outdoor Use	Yes		
Automatic Restart	Yes		
Operating and Electrical		Wiring	
Input Voltage	120 V	Wire Striplength	0.50/0.375 mm
Input Frequency	60 Hz	Lamp Connection	Series
Max THD	25 %	Wire Length by Color	See data sheet
Starting Method	Preheat	Wire Gauge (Nom)	18AWG mm
Lamp Current Crest Factor (Nom)	1.5	Wire Type	Solid
Ignition Time (Nom)	1 s	Remote Wiring Configuration Allowed	Yes
Inp. Current (Open Circuit)	0.41	Tandem Wiring Configuration Allowed	No
Input Current (Starting)	0.33	Through Wiring Configuration Allowed	No
Ballast Factor (Nom)	0.83	Max Ballast-Lamp Distance Remote Wiring	30'
Power Factor (Nom)	0.98	Max Ballast-Lamp Distance Tandem Wiring	-
Input Current (Operating) (Nom)	0.24 A	Max Ballast-Lamp Distance Through Wiring	-
Input Power (Nom)	28 W	Mechanical and Housing	
		Housing Material	Metal
		Housing	T1
		Housing Dimensions	6.5" x 2.38" x 1.5"
		Approval and Application	
		EMC Immunity Standard	FCC Non-Consumer

Standard

Approbation Marks	CSA certificate UL certificate RoHS Compliant
Sound Rating	A
UL Recognized	No
Product Data	
Order product name	STANDARD MAG BALLAST (1) 26W COMPACT(2-PIN) 120V

EAN/UPC - Product	781087068298
Order code	H1Q26TPWM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913700506809
Net Weight (Piece)	1.067 kg

Dimensional drawing



Product	A1	A2	B1	C1
STANDARD H1Q26TPWM	6.5 in	6 in	2.38 in	1.5 in

MAG BALLAST (1) 26W COMPACT(2-PIN) 120V

