



Core & Coil (71A) MH ~LT~ 175W

CORE & COIL HID MH BAL 100W M90/140 120/277/347V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information				
ANSI Code	M90-M140			
Lamp Type	100 MH			
Number of Lamps	1 piece/unit			
Circuit Type	HX-HPF			
Ballast Type	Magnetic HID			
Base Model	71A53A0			
Core Size	3 X 4 (2 coil)			
Suitable For Outdoor Use	Yes			
Ignitor Catalog Number	LI533-H4			
Ignitor Temperature Rating	105°C			
Capacitor Value	12 MFD			
Capacitor Catalog Number	7C120M30RA			
Capacitor Requirements	280V			
Capacitor Temperature Rating	105°C			
Capacitor Diameter/Oval Dimensions	1.65 in			
Capacitor Height	2.75 in			
Automatic Restart	No			

Operating and Electrical	
Input Voltage	120/277/347 V
Input Frequency	60 Hz
Input Current (Open Circuit)	2.6/1.15/1 A
Input Current (Starting)	1.15/0.5/0.4 A
Input Current (Short Circuit)	0.7-1.2/0.3-0.5/0.25-0.45 A
Secondary Short Circuit Current	1.3-1.6 A
Constant Wattage Deviation	12%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	280 V
Input Current (Nom)	1.15/0.5/0.4 A A
Input Power (Nom)	129 W
Rated Lamp Power	100 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) MH ~LT~ 175W

Max Ballast-Lamp Distance Remote	25'
Wiring	
Recommended Fuse Value	6/3/2 A
Approval and Application	
Open Circuit Voltage Test (Volts)	250-315 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	B/B/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

Product Data					
Order product name	CORE & COIL HID MH BAL 100W M90/140				
	120/277/347V KIT				
EAN/UPC - Product	781087078167				
Order code	913700533109				
Numerator - Quantity Per Pack	1				
Numerator - Packs per outer box	1				
Material Nr. (12NC)	913700533109				
Net Weight (Piece)	2.935 kg				

Dimensional drawing



MH BAL 100W M90/140 120/277/347V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 100W	2.9 in	1.7 in	3.9 in	3.5 in	2.8 in	2.4 in
M90/140 120/277/347V KIT						

