



Core & Coil (71A) MH 175W - 450W

CORE & COIL HID MH BAL 350W M131 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data


General Information		Electrical	
ANSI Code	M131-M171	Input Frequency	60 Hz
Lamp Type	350W MH	Input Current (Open Circuit)	2.2/1.3/1.1/1 A
Number of Lamps	1 piece/unit	Input Current (Starting)	2.2/1.3/1.1/1 A
Circuit Type	SUPER-CWA	Input Current (Short Circuit)	1.75-2.65/1.0-1.55/0.9-1.35/0.75-1.15 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	3.25-4 A
Base Model	71A5993A	Constant Wattage Deviation	10%
Core Size	4 1/4 x 4 3/4 (2 coil)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI533-H4	Open Circuit Voltage	270 V
Ignitor Temperature Rating	105°C	Input Current (Nom)	3.4/2/1.7/1.5 A A
Capacitor Value	22.5 MFD	Input Power (Nom)	400 W
Capacitor Catalog Number	7C225P40	Rated Lamp Power	350 W
Capacitor Requirements	345V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.75 in	Wire Length by Color	12"
Capacitor Height	4.8 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote	2'
Input Voltage	120/208/240/277 V	Wiring	

Core & Coil (71A) MH 175W - 450W

Recommended Fuse Value	10/7/5/5 A
Approval and Application	
Open Circuit Voltage Test (Volts)	240-300 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	D/C/C/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data	
Order product name	CORE & COIL HID MH BAL 350W M131 QUAD KIT
EAN/UPC - Product	781087097502
Order code	193136
Local order code	193136
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700535509
Net Weight (Piece)	5.194 kg

Dimensional drawing



MH BAL 350W M131 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 350W M131 QUAD KIT	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in

