



# Core & Coil (71A) HPS ~GT~ 400W

## CORE & COIL HID HPS BAL 750W S111 120/208/240V C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	S111
Lamp Type	750W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A86E5
Core Size	4 1/4 x 6
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI561-H5
Ignitor Temperature Rating	105°C
Capacitor Value	75 MFD
Capacitor Catalog Number	7C750S28RA
Capacitor Requirements	280V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	2.05 in
Capacitor Height	5 in
Automatic Restart	No

Operating and Electrical	
Input Voltage	120/208/240 V
Input Frequency	60 Hz
Input Current (Open Circuit)	3/1.75/1.6 A
Input Current (Starting)	6.3/3.7/3.2 A
Input Current (Short Circuit)	4.4-6.5/2.5-3.85/2.2-3.4 A
Secondary Short Circuit Current	9.2-11.25 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	220 V
Input Current (Nom)	6.75/4/3.5 A A
Input Power (Nom)	840 W
Rated Lamp Power	750 W


Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes

## Core & Coil (71A) HPS ~GT~ 400W

Max Ballast-Lamp Distance Remote Wiring 5'	
Recommended Fuse Value	20/10/10 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	200-245 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	D/E/E
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029E

<b>Product Data</b>	
Order product name	CORE & COIL HID HPS BAL 750W S111 120/208/240V C&C
EAN/UPC - Product	781087865552
Order code	913700539909
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	913700539909
Net Weight (Piece)	10.429 kg

### Dimensional drawing



HPS BAL 750W S111 120/208/240V C&C

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID 71A86E5500D	5.10 in	3.15 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

