



# Core & Coil (71A) HPS ~GT~ 400W

## CORE & COIL HID HPS BAL 1000W S52 480V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information			
ANSI Code	S52	Input Frequency	60 Hz
Lamp Type	1000W HPS	Input Current (Open Circuit)	0.9 A
Number of Lamps	1 piece/unit	Input Current (Starting)	1.6 A
Circuit Type	CWA	Input Current (Short Circuit)	1.75-2.65 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	6.4-7.8 A
Base Model	71A8743	Constant Wattage Deviation	Within Trapezoid
Core Size	4 1/4 x 6	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI571-H5	Open Circuit Voltage	435 V
Ignitor Temperature Rating	105°C	Input Current (Nom)	2.3 A A
Capacitor Value	26 MFD	Input Power (Nom)	1100 W
Capacitor Catalog Number	RW1626020	Rated Lamp Power	1000 W
Capacitor Requirements	525V	Wiring	
Capacitor Temperature Rating	90°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.75 in	Wire Length by Color	12"
Capacitor Height	4.25 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote Wiring	15'
Input Voltage	480 V	Recommended Fuse Value	6 A

## Core & Coil (71A) HPS ~GT~ 400W

### Approval and Application


Open Circuit Voltage Test (Volts)	395-485 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

### Product Data

Order product name	CORE & COIL HID HPS BAL 1000W S52 480V KIT
--------------------	---

EAN/UPC - Product	781087874318
Order code	193540
Local order code	193540
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700540109
Net Weight (Piece)	13.776 kg

### Dimensional drawing



HPS BAL 1000W S52 480V KIT

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID HPS BAL 1000W S52 480V KIT	5.90 in	3.90 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

