



Core & Coil (71A) HPS 200W - 400W

CORE & COIL HID HPS BAL 200W S66 480V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information			
ANSI Code	S66	Input Frequency	60 Hz
Lamp Type	200W HPS	Inp. Current (Open Circuit)	0.35 A
Number of Lamps	1 piece/unit	Input Current (Starting)	0.38 A
Circuit Type	CWA	Input Current (Short Circuit)	0.25-0.4 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	2.8-3.4 A
Base Model	71A8940	Constant Wattage Deviation	Within Trapezoid
Core Size	4 x 4 (2 coil)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI501-H4	Nominal Open Circuit Voltage	185 V
Ignitor Temperature Rating	105°C	Input Current (Operating) (Nom)	0.56 A A
Capacitor Value	28 MFD	Input Power (Nom)	240 W
Capacitor Catalog Number	7C280P30RA	Rated Lamp Watts	200 W
Capacitor Requirements	280V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.85 in	Wire Length by Color	12"
Capacitor Height	3.70 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote Wiring	2'
Input Voltage	480 V	Recommended Fuse Value	2 A

Core & Coil (71A) HPS 200W - 400W

Approval and Application


Open Circuit Voltage Test (Volts)	165-205 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

Product Data

Order product name	CORE & COIL HID HPS BAL 200W S66 480V KIT
--------------------	--

EAN/UPC - Product	781087894019
Order code	71A8940001D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700540209
Net Weight (Piece)	4.278 kg

Dimensional drawing



HPS BAL 200W S66 480V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A8940001D	3 in	1.170 in	4.8 in	4.4 in	4.3 in	3.9 in

