



# **Transformers**

# AUTO-TRANSFORMER AUTOXFMR 277:115 300VA C&C

Stepdown transformers and autotransformers are used when you need to connect a lower voltage device to a higher voltage source.

#### **Product data**


General Information	
Circuit Type	Transformer
Ballast Type	Magnetic HID
Base Model	71A9741
Core Size	7/8" E/I
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	277:120 or 120:277 V
Input Frequency	60 Hz
Input Current (Nom)	1.1 A
Rated Lamp Power	300 VA load W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed Yes	
Mechanical and Housing	
Housing	NA

Housing Dimensions	NA
Approval and Application	
Approval Marks	ULR RoHS Compliant
Temperature Marking	NA
UL Recognized	Yes
UL Insulation Class	H(180°C)
UL Temperature Code	NA
Product Data	
Order product name	AUTO-TRANSFORMER AUTOXFMR 277:115
	300VA C&C
EAN/UPC - Product	781087974162
Order code	913700550709
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913700550709
Net Weight (Piece)	1.475 kg

Datasheet, 2019, March 22 data subject to change

## **Transformers**

### Dimensional drawing



AUTO-TRANSFORMER AUTOXFMR 277:115 300VA C&C

Product
C1
C2
A1
A2
B1
B2

AUTO-TRANSFORMER AUTOXFMR 277:115
3.5 in 2 in 2.6 in 2.2 in 2.2 in 2.2 in 3.8 in 300VA C&C
2.2 in 2.2 in 3.8 in 3.8 in 3.0 i



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.