



Transformers

AUTO-TRANSFORMER AUTOXFMR 347:120/277 395VA C&C

Stepdown transformers and autotransformers are used when you need to connect a lower voltage device to a higher voltage source.

Product data


| General Information | |
|-------------------------------------|-----------------|
| Circuit Type | Transformer |
| Ballast Type | Magnetic HID |
| Base Model | 71A9862 |
| Core Size | 7/8" E/I |
| Suitable For Outdoor Use | Yes |
| Operating and Electrical | |
| Input Voltage | 347:(120/277) V |
| Input Frequency | 60 Hz |
| Input Current (Operating) (Nom) | 0.92 A |
| Rated Lamp Watts | 395 VA load W |
| Wiring | |
| Wire Striplength | 0.5 mm |
| Wire Length by Color | 12" |
| Wire Type | Stranded |
| Remote Wiring Configuration Allowed | Yes |
| Mechanical and Housing | |
| Housing | NA |

| Housing Dimensions | NA |
|--------------------------|--------------------------------|
| Approval and Application | |
| Approbation Marks | CSA certificate RoHS Compliant |
| Temperature Marking | NA |
| UL Recognized | No |
| UL Insulation Class | H(180°C) |
| UL Temperature Code | NA |

| Product Data | |
|---------------------------------|--|
| Order product name | AUTO-TRANSFORMER AUTOXFMR 347:120/277 395VA C&C |
| EAN/UPC - Product | 781087046869 |
| Order code | 71A9862600 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 8 |
| Material Nr. (12NC) | 913700579009 |
| Net Weight (Piece) | 1.910 kg |

Transformers

Dimensional drawing



| Product | C1 | C2 | A1 | A2 | B1 | B2 |
|-----------------------------|--------|--------|--------|--------|--------|--------|
| AUTO-TRANSFORMER 71A9862600 | 3.9 in | 2.7 in | 2.6 in | 2.2 in | 2.2 in | 1.8 in |

AUTO-TRANSFORMER 71A9862600

