



Indoor Enclosed (78E)

INDOOR ENCLOSED HID MH BAL 1000W M47 QUAD ENCL

These units are designed for use indoors where the ballast must be mounted remotely from the luminaire. These ballasts are typically used in applications where the luminaire is mounted in an area with very high ambient temperatures. The ballast can be mounted remotely in a cooler location.

Product data

General Information			
ANSI Code	M47	Open Circuit Voltage	430 V
Lamp Type	1000W MH	Input Current (Nom)	9/5.2/4.5/3.9 A A
Number of Lamps	1 piece/unit	Input Power (Nom)	1080 W
Circuit Type	CWA	Rated Lamp Power	1000 W
Ballast Type	Magnetic HID		
Base Model	78E6592	Wiring	
Suitable For Outdoor Use	No	Wire Striplength	0.5 mm
Ignitor Catalog Number	NA	Wire Length by Color	12"
Capacitor Catalog Number	Inside Can	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
		Max Ballast-Lamp Distance Remote Wiring	Determined by AWG used
Operating and Electrical		Recommended Fuse Value	20/15/10/10 A
Input Voltage	120/208/240/277 V		
Input Frequency	60 Hz	Mechanical and Housing	
Input Current (Open Circuit)	4.5/2.7/2.3/2.2 A	Housing Material	Metal
Input Current (Starting)	7.8/4/3.7/3.2 A	Housing	IE
Input Current (Short Circuit)	5.7-8.5/3.2-4.8/2.8-4.3/2.4-3.6 A	Housing Dimensions	14.44" x 5.75" x 7.69"
Secondary Short Circuit Current	5.2-6.4 A		
Constant Wattage Deviation	10%	Approval and Application	
Ballast Factor (Nom)	1	Open Circuit Voltage Test (Volts)	385-475 V
Power Factor (Nom)	0.90	Approval Marks	CSA certificate UL certificate RoHS Compliant

Indoor Enclosed (78E)


Temperature Marking	Max. ambient temperature 55°C
UL Recognized	No
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	NA

Product Data

Order product name	INDOOR ENCLOSED HID MH BAL 1000W M47 QUAD ENCL
--------------------	---

EAN/UPC - Product	781087865927
Order code	505461
Local order code	505461
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700583009
Net Weight (Piece)	0.010 kg

Dimensional drawing



MH BAL 1000W M47 QUAD ENCL

Product	A1	A2	A3	A4	B1	B2	C1	D1
INDOOR ENCLOSED HID MH BAL 1000W M47 QUAD ENCL	14.4 in	13.4 in	12.7 in	12.1 in	7.7 in	3.3 in	5.8 in	0.4 in

