



# e-Vision Low Wattage 20-150W

## E-VISION ELE MH BAL 39W M130 / C179 120V

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

### Product data

General Information		Rated Lamp Power	
ANSI Code	C130-M130,C179	Rated Lamp Power	39 W
Lamp Type	39W MH	Wiring	
Number of Lamps	1 piece/unit	Color Input Terminals	No terminals
Ballast Type	Electronic HID	Color Output Terminals	No terminals
Base Model	RMH39KLFS	Wire Striplength	0.50 mm
Suitable For Outdoor Use	Yes	Control Wire Gauge	NA
Operating and Electrical		Wire Length by Color	All leads = 6"
Input Voltage	120 V	Wire Gauge (Nom)	18AWG mm
Input Frequency	50 to 60 Hz	Wire Type	Stranded
Total Harmonic Distortion USA	15 %	Remote Wiring Configuration Allowed	Yes
Crestfactor (Nom)	1.8	Tandem Wiring Configuration Allowed	No
Ignition Time (Nom)	1200 s	Through Wiring Configuration Allowed	No
Ballast Factor (Nom)	1	Connector Type	No connector
Power Factor (Nom)	0.90	Temperature	
Input Current (Max)	0.4 A	T-Case Maximum (Nom)	90 °C
Input Current (Min)	0.4 A	Mechanical and Housing	
Input Power (Nom)	45 W	Housing Material	Metal

## e-Vision Low Wattage 20-150W

Housing	K
Housing Dimensions	4.1" x 1.3" x 1.2"

### Approval and Application


EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No

### Product Data

Order product name	E-VISION ELE MH BAL 39W M130 / C179 120V
--------------------	--

EAN/UPC - Product	781087051252
Order code	120345
Local order code	120345
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700611988
Net Weight (Piece)	0.196 kg

## Dimensional drawing



E-VISION RMH39KLFSM

Product	A1	A2	A3	B1	B2	C1
E-VISION ELE MH BAL 39W M130 / C179 120V	4.4 in	4.1 in	4.5 in	1.1 in	0.5 in	1.2 in

