



# e-Vision Low Wattage 20-150W

## E-VISION ELE MH BAL 39W M130 / C179 120V

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

### Product data


General Information		Rated lamp power	
ANSI Code	C130-M130,C179	39 W	
Lamp type	39W MH	Wiring	
Number of lamps	1 piece/unit	Colour input terminals	No terminals
Ballast type	Electronic HID	Colour output terminals	No terminals
Base model	RMH39KLFS	Wire strip length	0.50 mm
Suitable for outdoor use	Yes	Control wire gauge	NA
Operating and Electrical		Wire length by colour	All leads = 6"
Input voltage	120 V	Wire gauge (nom.)	18AWG mm
Input frequency	50 to 60 Hz	Wire type	Stranded
Total harmonic distortion USA	15 %	Remote wiring configuration allowed	Yes
Crest factor (nom.)	1.8	Tandem wiring configuration allowed	No
Ignition time (nom.)	1200 s	Through-wiring configuration allowed	No
Ballast factor (nom.)	1	Connector type	No connector
Power factor (nom.)	0.90	Temperature	
Input current (max.)	0.4 A	T-Case maximum (nom.)	90 °C
Input current (min.)	0.4 A	Mechanical and Housing	
Input power (nom.)	45 W	Housing material	Metal

e-Vision Low Wattage 20-150W

Housing	K
Housing dimensions	4.1" x 1.3" x 1.2"
Approval and Application	
EMC immunity standard	FCC Non-Consumer
Approval marks	CSA certificate UL certificate RoHS Compliant
Humming and noise level	A
UL recognised	No
Product Data	
Order product name	E-VISION ELE MH BAL 39W M130 / C179 120V

EAN/UPC – product	781087051252
Order code	913700611988
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	913700611988
Net weight (piece)	0.196 kg

Dimensional drawing



Product	A1	A2	A3	B1	B2	C1
E-VISION ELE MH BAL 39W M130 / C179 120V	4.4 in	4.1 in	4.5 in	1.1 in	0.5 in	1.2 in

E-VISION RMH39KLFSM

