



# e-Vision Low Wattage 20-150W

## E-VISION ELE MH BAL 39W M130 / C179 120V

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

### Product data

General Information	
ANSI Code	C130-M130,C179
Lamp Type	39W MH
Number of Lamps	1 piece/unit
Ballast Type	Electronic HID
Base Model	RMH39KLFS
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	120 V
Input Frequency	50 to 60 Hz
Total Harmonic Distortion USA	15 %
Crestfactor (Nom)	1.8
Ignition Time (Nom)	1200 s
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Input Current (Max)	0.4 A
Input Current (Min)	0.4 A
Input Power (Nom)	45 W

Rated Lamp Power	39 W
Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.50 mm
Control Wire Gauge	NA
Wire Length by Color	All leads = 6"
Wire Gauge (Nom)	18AWG mm
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Connector Type	No connector
Temperature	
T-Case Maximum (Nom)	90 °C
Mechanical and Housing	
Housing Material	Metal

## e-Vision Low Wattage 20-150W

Housing	K
Housing Dimensions	4.1" x 1.3" x 1.2"

### Approval and Application


EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No

### Product Data

Order product name	E-VISION ELE MH BAL 39W M130 / C179 120V
--------------------	------------------------------------------

EAN/UPC - Product	781087051252
Order code	913700611988
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700611988
Net Weight (Piece)	0.196 kg

## Dimensional drawing



E-VISION RMH39KLF5M

Product	A1	A2	A3	B1	B2	C1
E-VISION ELE MH BAL 39W M130 / C179 120V	4.4 in	4.1 in	4.5 in	1.1 in	0.5 in	1.2 in

