



Primaline Halogen Transformers

Primaline 150 230-240V 50/60Hz

Philips Primaline is a high-frequency electronic halogen transformer suitable for low-voltage 12 V halogen lamps. It offers ultimate performance and is built with overload and short circuit protection to IEC and ENEC standards. It is available in 70, 105 and 150 W versions and fits in small down light halogen applications.

Warnings and Safety

• Transformer is not suitable for DC operation

Product data


Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Temperature	
T-Case Lifetime (Nom)	65 ℃
T-Case Maximum (Max)	80 ℃
Approval and Application	
Approval Marks	SELV CE marking ENEC certificate

Product Data		
Order product name	Primaline 150 230-240V 50/60Hz	
Full product name	Primaline 150 230-240V 50/60Hz	
Full product code	871150091270130	
Order code	913700627791	
Material Nr. (12NC)	913700627791	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8711500912701	
Numerator - Packs per outer box	50	
EAN/UPC - Case	8711500912718	

Datasheet, 2023, September 4 data subject to change

Primaline Halogen Transformers

Dimensional drawing



Product	C1	A1	B1
Primaline 150 230-240V 50/60Hz	33 mm	145 mm	51 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.