



# Certaline Halogen Transformers

## Certaline 60W 230-240V 50/60Hz

Electronic halogen transformer for low voltage halogen lamps the range include Certaline 60W 230-240V and Certaline105W 230-240V

### Warnings and Safety

- Transformer is not suitable for DC operation
- Transformer is not suitable for DC operation


### Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Temperature	
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	75 °C
Approval and Application	
Approval Marks	SELV CE marking VDE marking

Product Data	
Order product name	Certaline 60W 230-240V 50/60Hz
Full product name	Certaline 60W 230-240V 50/60Hz
Full product code	871150091378430
Order code	913700633891
Material Nr. (12NC)	913700633891
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500913784
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500913791

# Certaline Halogen Transformers

## Dimensional drawing



Product	C1	A1	B1
Certaline 60W 230-240V 50/60Hz	22.0 mm	107.0 mm	32.0 mm

