



Certaline Halogen Transformers

CERTALINE 150W 230-240V 50/60HZ

Electronic halogen transformer for low voltage halogen lamps the range include Certaline 60W 230-240V and Certaline105W 230-240V

Warnings and Safety

- Transformer is not suitable for DC operation


Product data

Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Temperature	
T-case lifetime (nom.)	65 °C
T-Case maximum (max.)	75 °C
Approval and Application	
Approval marks	SELV CE marking VDE marking
Product Data	
Order product name	Certaline 150W 230-240V 50/60Hz

Full product name	CERTALINE 150W 230-240V 50/60HZ
Full EOC	871150091385230
Order code	91385230
Material no. (12 NC)	913700634091
Local order code	CERTALINE150W
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500913852
Numerator – packs per outer box	50
EAN/UPC - Case	8711500913869

Certaline Halogen Transformers

Dimensional drawing



Product	C1	A1	B1
Certaline 150W 230-240V 50/60Hz	36.0 mm	180.0 mm	46.0 mm

